

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO HOME™

RL4 | Lumen Select

4-inch All-purpose LED retrofit module with Bluetooth® Mesh connectivity

Typical Applications

Residential

Interactive Menu

- Order Information [page 2](#)
- Product Specifications [page 3](#)
- Photometric Data [page 4](#)
- Energy & Performance Data [page 4](#)
- Product Warranty

Product Certification




Product Features




Top Product Features

- Selectable lumens: set max lumen output to 600 or 900 lumens
- Adjustable white tuning: 2700K - 5000K, 90 CRI
- Connect to the HALO Home Bluetooth Mesh network, no hub required
- Suitable for new construction, remodel and retrofit
- Listed for use with HALO 4" housings. Classified for use with other 4" housings

Dimensional and Mounting Details



Scale



Order Information

Icon Key:  Configurable Product

SAMPLE ORDER NUMBER: **RL4099BLE40AWH**

Models	Lumens	CRI/CCT	Protocol	Finish
--------	--------	---------	----------	--------

Standard Driver 120-277VAC, 0-10V analog dimming

Models	Lumens	CRI/CCT	Protocol	Finish
RL4 = 4" all- purpose retrofit LED module	09 = 900 lumens (nominal)	9 = 90 CRI minimum, white tuning, select CCT 2700K – 5000K, in the mobile app	BLE40A = Bluetooth Mesh wireless control, 4.0	WH = Matte white baffle
Notes	Notes	Notes	Notes	Notes

Accessories

Accessories
<p>Designer Trims</p> <p>RL4TRMWHB = 4" White Paintable Trim Ring, Baffle</p> <p>RL4TRMSNB = 4" Satin Nickel Trim Ring, Baffle</p> <p>RL4TRMTBZB = 4" Tuscan Bronze Trim Ring, Baffle</p> <p>RL4TRMWH = 4" White Paintable Trim Ring</p> <p>RL4TRMSN = 4" Satin Nickel Trim Ring</p> <p>RL4TRMTBZ = 4" Tuscan Bronze Trim Ring</p>
Notes

Product Specifications

Wireless System

- For use with the HALO Home mobile app
- Bluetooth low energy (BLE) mesh allows on/off, white tuning and lumen output to be controlled wirelessly with companion wall switches, smart phones and tablets using HALO Home mobile application
- Setup groups, scenes and schedules to automate lighting with the HALO Home mobile app

Wireless Pairing

- See HALO Home Quick Start Guide for wireless setup, guidance and troubleshooting: www.cooperlighting.com

Bluetooth Mesh

- HALO Home products work better together. Smartphone(s) will need to be within range of HALO Home device to control
- Expand and strengthen the Bluetooth network range by adding HALO Home devices. Learn more at www.cooperlighting.com

Module - Trim

- Module construction includes LED array, heat sink, reflector, lens, baffle and trim ring
- Regressed baffle
- Heat sink designed to conduct heat away from the LED array, keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments

LED Array

- Use the HALO Home app to set maximum light output - choose between 600 or 900 lumens
- Mid power LED array provides a uniform source with high efficiency and no pixilation
- 90 CRI minimum, R9 greater than 50
- Color accuracy within 3 SDCM at the CCT endpoints and 4 SDCM in between endpoints, provide color accuracy and uniformity
- Color Temperature (CCT) has an adjustable range from 2700K to 5000K within the mobile app (factory default 3000K)
- 50,000 hour life

Optical Assembly

- Regressed lens
- Impact-resistant polycarbonate
- Convex form and lamp-like appearance
- Diffuse for even illumination

Driver

- Integral 120V 60 Hz constant current driver provides noise free operation
- Inline electrical quick connect and E26 adapter (included) provides mains connections
- Consult instruction sheets and Quick Start Guide for more information

Dimming

- Continuous, flicker-free dimming from 100% to 5%
- Only dimmable with HALO Home devices or app

Retention

- Push-N-Twist universal installation clips
- Clips are pre-installed and designed to fit 4" compatible recessed housings

Designer Skins (sold separately)

- RL4 skins are accessory rings that attach to the RL4 for a permanent finish. Refer to the RL4 accessories specification sheet for details
 - White (Paintable)
 - Satin Nickel
 - Tuscan Bronze

Gaskets

- Closed cell gaskets achieve restrictive airflow requirements without additional caulking

Compliance


- UL Certified for use with Halo housings and other's housings
- Wet and Damp location listed
- Airtight certified per ASTM-E283
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy luminaire compliance. Complies with Title 24 JA8-2016-E
- Can be used International Energy Conservation Code (IECC) high efficiency luminaire compliance
- ENERGY STAR® listed, reference database for current listings
- FCC ID: 2AKCY-RL4HLBLE
- IC Code: 4706A-RL4HLBLE

Warranty

- Five-year limited warranty, consult website for details. www.cooperlighting.com

Photometric Data

[View IES files](#)



RL4099BLE40AWH-3000K
 Spacing criterion: (0-180) 1.16
 (90-270) 1.16
 (Diagonal) 1.2
 Beam Angle: 84.9°
 Field Angle: 136.8°
 Lumens: 973
 Input Watts: 10.6 W
 Efficacy: 91.79 LPW
 Test Report:
 RL4099BLE40AWH-3000K.ies


Zonal Lumen	Lumens	% Lumens
0-30	376.6	38.7
0-40	585.7	60.2
0-60	864.0	88.8
0-90	973.0	100

Note: Refer to IES files for more product data.

Energy and Performance Data

Color Metrics - TM-30-15 & CRI/CIE (3000K)

TM-30-15	Rf = 91
	Rg = 100
CRI/CIE	Ra = 92
	R9 = 69




Color Temperature Multipliers

		LUMENS	POWER (W)	LPW
App Adjustable CCT	2700K	956	10.6	90.2
	3000K	973	10.9	89.3
	3500K	984	10.9	90.3
	4000K	992	10.9	91.0
	5000K	998	10.9	91.6

Dimensional Details

Designer Trim - Baffle



Designer Trim - Splay

