Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's	name or	trade mark:	PHILIPS
------------	---------	-------------	---------

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

Model identifier:	9290036243
-------------------	------------

Type	of I	ight	sour	ce:
IVDC	U I I	ISIIL	JUUI	···

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type	E27		
(or other electric interface)			
Mains or non-mains:	MLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

Product parameters

Froduct parameters				
Parameter		Value	Parameter	Value
General product parameters:				
<u> </u>	mption in on- 00 h), rounded st integer	6	Energy efficiency class	А
Useful luminous flux (фuse), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		1 095 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	2 700
On-mode power (P _{on}), expressed in W		5,2	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00
Networked standby power (P _{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	80
Outer dimen-	Height	104	Spectral power dis-	See image
sions without	Width	60	tribution in the	in last page
separate con- trol gear, light- ing control	Depth	60	range 250 nm to 800 nm, at full-load	

parts and non- lighting con- trol parts, if any (millime- tre)				
Claim of equivalent power ^(a)	Yes	If yes, equivalent power (W)	75	
		Chromaticity coordi-	0,470	
		nates (x and y)	0,429	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	9 0	Survival factor	0,90	
the lumen maintenance factor	0,96			
Parameters for LED and OLED mains light sources:				
displacement factor (cos φ1)	0,50	Colour consistency in McAdam ellipses	6	
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	-	If yes then replace- ment claim (W)	-	
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,4	

(a)'-': not applicable; (b)'-': not applicable;

