



CoreLine tubular waterproof

WT210C LED70S/840 PSU TW1 PC L1500

CoreLine tubular waterproof, 54 W, L1500 mm, 7000 lm, 4000 K, Very wide beam, Opal, IP68, IK10, TW1

CoreLine Tubular Waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, efficient luminaire with a very long lifetime, CoreLine Tubular Waterproof comes in two versions to meet various applications needs. The ammonia-resistant and sealed luminaire (PMMA tube) is suitable for animal lighting, livestock and food applications, while the PC version offers a modern and industrial design that is suitable for a wide range of general lighting applications. Both versions come with significant dust, water and impact protection, making them relevant for specific applications. CoreLine Tubular Waterproof WT210C luminaires promise energy savings and less maintenance. At the same time, they can be installed in next to no time and without tools, thanks to pre-installed through-wiring and an external connector, which mean the luminaire does not require opening. These waterproof lighting solutions are flexible to mount on ceilings or suspended in both indoor and outdoor environments.

Product data

General Information		Warranty period	
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Feed-through wiring	Feed-through wiring 1-phase	Glow-wire test	Temperature 850 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Performance		
CE mark	Yes		

CoreLine tubular waterproof

Light Technical	
Luminous Flux	7,000 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Light source color	840 neutral white
Optic type	Very wide beam
Luminaire light beam spread	130°
Unified glare rating CEN	26

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	40 A
Inrush time	0.1 ms
Power Consumption	54 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	18

Temperature	
Ambient temperature range	-20 to +40 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,615 mm
Overall width	82,5 mm

Overall height	82.5 mm
Overall diameter	82.5 mm
Dimensions (Height x Width x Depth)	83 x 83 x 1615 mm

Approval and Application	
Ingress protection code	IP68 [Dust penetration-protected, pressure watertight]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Product Data	
Order product name	WT210C LED70S/840 PSU TW1 PC L1500
Full product name	WT210C LED70S/840 PSU TW1 PC L1500
Full product code	871951494738299
Order code	911401828184
Material Nr. (12NC)	911401828184
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514947382
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514947429

CoreLine tubular waterproof

Dimensional drawing

