



# CoreLine panel

## RC132V G5 31\_36\_43S/840 PSU W60L60 NOC

CoreLine panel, All-in, 34.5 W, 24.5 W, 600x600 mm, 3100 lm, 3600 lm, 4300 lm, 4000 K

Philips CoreLine panel Gen5 delivers on the CoreLine promise of innovation, easy installation and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative MultiLumen feature offers a choice of three lumen packages in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing this CoreLine RC132V LED panel is quick and easy too, thanks to a quick connector or Wieland connector. Interact Ready luminaires with integrated wireless communications are also available in this CoreLine range, ready to be used with Interact gateways, sensors and software.

### Product data

General Information		EU RoHS compliant	
Light source replaceable	No		Yes
Number of gear units	1 unit	Light Technical	
Driver included	Yes	Luminous Flux	3,100 3,600 4,300 lm
Lighting Technology	LED	Saturated Red (R9)	<50
Value ladder	Performance	Correlated Color Temperature (Nom)	4000 K
CE mark	Yes	Luminous Efficacy (rated) (Nom)	125 lm/W
Warranty period	5 years	Color rendering index (CRI)	≥80
Flammability mark	For mounting on normally flammable surfaces	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
ENEC mark	ENEC mark	Stroboscopic effect visibility measure (SVM)	0.4
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	840 neutral white
		Optic type	Beam angle 120°

# CoreLine panel

Luminaire light beam spread	120°
Unified glare rating CEN	22
All-in Type	All-in, Multi Lumen

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	19.7 A
Inrush time	0.242 ms
Power Consumption	34.5 24.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	13

## Temperature

Ambient temperature range	-10 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Steel
Reflector material	Acrylate
Optic material	Polystyrene
Optical cover material	Acrylate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	595 mm
Overall width	595 mm
Overall height	61 mm
Dimensions (Height x Width x Depth)	61 x 595 x 595 mm

## Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
-------------------------	--

Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM≤3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L75

## Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

## Product Data

Order product name	RC132V G5 31_36_43S/840 PSU W60L60 NOC
Full product name	RC132V G5 31_36_43S/840 PSU W60L60 NOC
Full product code	871951495035100
Order code	911401844184
Material Nr. (12NC)	911401844184
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514950351
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514950351

## CoreLine panel

### Dimensional drawing

