



# CoreLine Wall-mounted

## WL140V LED20S/840 PSU MDU WH

CoreLine Wall-mounted, 19 W, D390 mm, 1950 lm, 4000 K, Sensor-based dim, MDU2, IP65

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to-install and high quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

### Product data

General Information		Light Technical	
Light source replaceable	Yes	Glow-wire test	Temperature 850 °C, duration 30 s
Number of gear units	1 unit	EU RoHS compliant	Yes
Driver included	Yes	Luminous Flux	1,950 lm
Lighting Technology	LED	Saturated Red (R9)	<50
Value ladder	Performance	Correlated Color Temperature (Nom)	4000 K
Embedded control	Programmable movement and light sensor	Luminous Efficacy (rated) (Nom)	100 lm/W
CE mark	Yes	Color rendering index (CRI)	>80
Warranty period	5 years	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Flammability mark	-	Stroboscopic effect visibility measure (SVM)	1.6
ENEC mark	ENEC mark		

## CoreLine Wall-mounted

Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Symmetrical
Luminaire light beam spread	120° x 120°
Unified glare rating CEN	24

### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	14 A
Inrush time	0.007 ms
Power Consumption	19 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	32

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	Sensor-based dim
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall height	85 mm
Overall diameter	390 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK10 [20 J vandal-resistant]
Sustainability rating	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.3818,0.3797) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life	5 %
50000 h	
Lumen maintenance at median useful life*	-
35000 h	
Lumen maintenance at median useful life*	80
50000 h	
Lumen maintenance at median useful life*	-
75000 h	
Lumen maintenance at median useful life*	-
100000 h	

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

### Product Data

Order product name	WL140V LED20S/840 PSU MDU WH
Full product name	WL140V LED20S/840 PSU MDU WH
Full product code	871951452878999
Order code	911401848082
Material Nr. (12NC)	911401848082
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514528789
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514528949

## CoreLine Wall-mounted

### Dimensional drawing

