# **PHILIPS** Lighting



# CoreLine Wallmounted

# WL140V LED12S/830 PSR MDU WH

CoreLine Wall-mounted, 13 W, D390 mm, 1200 lm, 3000 K, Sensor-based dim, MDU3, IP65

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to install and high quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

#### Product data

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Performance
Embedded control	Programmable movement and light
	sensor with wireless grouping
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark

Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	1,200 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as	1
per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	1.6

## CoreLine Wall-mounted


Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Symmetrical
Luminaire light beam spread	120° x 120°
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	10 A
Inrush time	0.066 ms
Power Consumption	13 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	32
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Sensor-based dim
Constant light output	No
Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Optical cover material Fixation material	Polycarbonate -
	Polycarbonate - White
Fixation material	-
Fixation material Housing Color	- White
Fixation material Housing Color Optical cover finish	- White Opal
Fixation material Housing Color Optical cover finish Overall height	- White Opal 85 mm
Fixation material Housing Color Optical cover finish Overall height	- White Opal 85 mm
Fixation material Housing Color Optical cover finish Overall height Overall diameter	- White Opal 85 mm

Mech. impact protection code	IK10 [20 J vandal-resistant]
Sustainability rating	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mn
	to EN62778
Photobiological risk specification	0.2 m
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.4338,0.4030) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	)
Control gear failure rate at median useful life	5 %
50000 h	
Lumen maintenance at median useful life*	-
35000 h	
Lumen maintenance at median useful life*	80
50000 h	
Lumen maintenance at median useful life*	
75000 h	
Lumen maintenance at median useful life*	-
100000 h	
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No
Product Data	
Order product name	WL140V LED12S/830 PSR MDU WH
Full product name	WL140V LED12S/830 PSR MDU WH
Full product code	871951453082999
Order code	911401851582
Material Nr. (12NC)	911401851582
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514530829
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514530881

2

### **CoreLine Wall-mounted**

#### Dimensional drawing





© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, March 21 - data subject to change