



# Ledinaire floodlights gen3

## BVP164 LED60/840 PSU 50W SWB CE

Ledinaire floodlights gen3, 50 W, 6000 lm, 4000 K, CRI80, Symmetrical wide beam, IP65

This Ledinaire floodlights range contains a selection of popular off-the-shelf LED luminaires that comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

### Product data

General Information		Standard tilt angle side entry	
Lamp family code	-	Correlated Colour Temperature	4000 K
Light source replaceable	No	Luminous efficacy (rated) (nom.)	120 lm/W
Number of gear units	Unit	Colour rendering index (CRI)	>80
Driver included	Yes	Flickering value (PstLM)	1
Light source engine type	LED	Stroboscopic effect	5
Lighting Technology	LED	Light source colour	840 neutral white
CE mark	Yes	Optical cover type	Glass
Warranty period	3 years	Luminaire light beam spread	110° x 110°
Flammability mark	-	Optic type outdoor	Symmetrical wide beam
ENEC mark	-		
Glow-wire test	Temperature 650 °C, duration 30 s	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz
		Initial CLO power consumption	- W
		Average CLO power consumption	50 W
		End CLO power consumption	- W
		Inrush current	1.68 A
Light Technical			
Upwards light output ratio	0		
Luminous Flux	6,000 lm		
Standard tilt angle post-top	-		

## Ledinaire floodlights gen3

Inrush time	0.0082 ms
Power Consumption	50 W
Power Factor (Fraction)	0.95
Connection	Flying leads/cables
Cable	Cable 1.0 m without plug
Number of products on MCB of 16 A type B	44

### Temperature

Ambient temperature range	-25 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover/lens material	Tempered glass
Fixation material	Steel
Housing Colour	Grey
Mounting device	Mounting bracket adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	173 mm
Overall width	232 mm
Overall height	26.1 mm
Effective projected area	0.028 m <sup>2</sup>
Dimensions (height x width x depth)	26 x 232 x 173 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 2 kV differential mode and 2 kV common mode

Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	80


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

### Product Data

Order product name	BVP164 LED60/840 PSU 50W SWB CE
Full product name	BVP164 LED60/840 PSU 50W SWB CE
Full EOC	871951453353099
Order code	53353099
Material no. (12 NC)	911401854483
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514533530
Numerator – packs per outer box	16
EAN/UPC - Case	8719514533776

## Dimensional drawing



## Ledinaire floodlights gen3

