



MASTER LEDtube InstantFit HF T8



MAS LEDtube HF 600mm HO 8W865 T8

Philips MASTER LEDtube InstantFit T8 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. Philips MASTER LEDtube InstantFit T8 is the ideal solution for customers who have higher light requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.

Product data

General Information		Operating and Electrical	
Cap-Base	G13 ROT	Luminous Efficacy (rated) (Nom)	131 lm/W
Nominal lifetime	75,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Photobiological safety according to EN 62471	RG0
CE mark	Yes	Line Frequency	20000-120000 Hz
EU RoHS compliant	Yes	Input Frequency	20000-120000 Hz
Color Code	865 [CCT of 6500K]	Power Consumption	8 W
Beam Angle (Nom)	160 degree(s)	Lamp Current (Max)	500 mA
Luminous Flux	1,050 lm	Lamp Current (Min)	150 mA
Color Designation	Cool Daylight	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	6500 K	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9

MASTER LEDtube InstantFit HF T8

Voltage (Nom)	20-50 V
LED alternative to fluorescent lamp power	18 W
Inrush current at mains	-
Max. lamp no. on MCB B type 10A – Mains	-
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	-
Max. lamp no. on MCB B type 16A – Mains	-
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	-
Ballast Compatibility	HF

Temperature

Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic

Product Length	600 mm
Bulb Shape	T8


Approval and Application

Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	1597258

Product Data

Order product name	MAS LEDtube HF 600mm HO 8W865 T8
Full product name	MAS LEDtube HF 600mm HO 8W865 T8
Full product code	871951446644900
Order code	929001393332
Material Nr. (12NC)	929001393332
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514466449
Numerator - Packs per outer box	20
EAN/UPC - Case	8719514466456


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube HF 600mm HO 8W865 T8	25.8 mm	28 mm	588.6 mm	595.7 mm	602.8 mm

MASTER LEDtube InstantFit HF T8


Photometric data



Light Distribution Diagram - MAS LEDtube HF 600mm HO 8W865 T8




Spectral Power Distribution Colour - MAS LEDtube HF 600mm HO 8W865 T8




Technical Drawing 01 Page Lighting 01 Page 1/1

General uniform lighting - MAS LEDtube HF 600mm HO 8W865 T8

Lifetime





Life Expectancy Diagram - MAS LEDtube HF 600mm HO 8W865 T8



Life Expectancy Diagram - MAS LEDtube HF 600mm HO 8W865 T8


MASTER LEDtube InstantFit HF T8

Lifetime



Lumen Maintenance Diagram - MAS LEDtube HF 600mm HO 8W865 T8

Lumen Maintenance Diagram - MAS LEDtube HF 600mm HO 8W865 T8



Life Expectancy Diagram - MAS LEDtube HF 600mm HO 8W865 T8

