



LED Highbay

165HB/LED/850/D NB DL BB G2 4/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	60 degree(s)
Luminous Flux	25,000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	151.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	165 W
Lamp Current (Nom)	1,650 mA
Starting Time (Nom)	0.5 s


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	HIB_UL Type B (UL Listed+Classified)
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	136 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	Others
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	165HB/LED/850/D NB DL BB G2 4/1
Full product name	165HB/LED/850/D NB DL BB G2 4/1
Order code	563998

LED Highbay

Material Nr. (12NC)	929002496604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677563998
Numerator - Packs per outer box	4



EAN/UPC - Case	50046677563993
----------------	----------------

Dimensional drawing




Product	D	C
165HB/LED/850/D NB DL BB G2 4/1	9-7/8 inch	11-1/4 inch

Photometric data



General uniform lighting - 165HB/LED/850/D NB DL BB G2 4/1


Light Distribution Diagram - 165HB/LED/850/D NB DL BB G2 4/1



Spectral Power Distribution Colour - 165HB/LED/850/D NB DL BB G2 4/1

LED Highbay

Lifetime



Life Expectancy Diagram - 165HB/LED/850/D NB DL BB G2 4/1

Lumen Maintenance Diagram - 165HB/LED/850/D NB DL BB G2 4/1

