MASTER Value LEDtube T8

MAS LEDtube VLE 1200mm UO 15.5W 830 T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance for use in all general lighting, office, industry, retail, and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	60,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	190 degree(s)
Luminous Flux	2,300 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	148.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Flickering value (PstLM) - Flickering value as per	1
EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	15.5 W
Lamp Current (Max)	73 mA
Lamp Current (Min)	67 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	36 W
Inrush current at mains	8.2
Max. lamp no. on MCB B type 10A - Mains	90



A ↑ G



Lighting


Datasheet, 2024, March 20

MASTER Value LEDtube T8

Max. lamp no. on MCB B type 10A - EM ballast	95
without Comp. Cap.	
Max. lamp no. on MCB B type 10A - EM ballast	15
with Comp. Cap.	
Max. lamp no. on MCB B type 16A - Mains	145
Max. lamp no. on MCB B type 16A - EM ballast	150
without Comp. Cap.	
Max. lamp no. on MCB B type 16A - EM ballast	25
with Comp. Cap.	
Ballast Compatibility	EM/Mains
Temperature	
Ambient temperature range	-20 ℃ to 45 ℃
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	Т8

Approval and Application	
Energy Efficiency Class	D
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking
	KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	1095871
Product Data	
Order product name	MAS LEDtube VLE 1200mm UO
	15.5W 830 T8
Full product name	MAS LEDtube VLE 1200mm UO
	15.5W 830 T8
Full product code	871951431680500
Order code	929002997602
Material Nr. (12NC)	929002997602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514316805
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514316812


Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube VLE 1200mm UO	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15.5W 830 T8					


MASTER Value LEDtube T8

Photometric data




	0	TLED 13.5W 1808K #240824975
		15DRM
No meta-hera	Questa ustrativo depun	USR dagram
12:20	A Shared United M	
TXX XX	hind	
HUS201		- Advant
KX XX	Last in the	
N N	HITTHE	-
- 1 W - 1 W	Utrace have been	Lament Title
Winners S	Conception of a state of a local state of the	
Marine Areal Trees		
And the second s		664646469
		664646464
		Tarra a far a far a far a far
	Contraction of the local distance of the loc	No.

Light Distribution Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8




Spectral Power Distribution Colour - MAS LEDtube VLE 1200mm UO 15.5W 830 T8

Lifetime



Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8


General uniform lighting - MAS LEDtube VLE 1200mm UO 15.5W 830 T8




Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8

MASTER Value LEDtube T8


Lifetime



Lumen Maintenance Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8



Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8



Lumen Maintenance Diagram - MAS LEDtube VLE 1200mm UO 15.5W 830 T8



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.