



LED Corn Cobs

150CC/LED/840/LS EX39 G2 BB 277-480V 3/1

Philips Corn Cob HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

| General Information | |
|---------------------------------------|---------------------------------|
| Cap-Base | EX39 [Exclusionary Mogul Screw] |
| Nominal lifetime | 50,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 23,500 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 156 lm/W |
| Color Consistency | ANSI 4000K quadrangle |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 150 W |
| Lamp Current (Nom) | 600 mA |
| Starting Time (Nom) | 1.5 s |


| Warm-up time to 60% light | 1.5 s |
|-------------------------------------|--|
| Power Factor (Fraction) | 0.9 |
| Voltage (Nom) | 277-480 V |
| UL Type | HIB_UL Type B (UL classified+RU) |
| Temperature | |
| Ambient temperature range | -20 °C to 55 °C |
| T-Case Maximum (Nom) | 38.4 °C |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Material | Plastic |
| Bulb Shape | Corncob |
| Application Conditions | |
| can it be used in closed luminaires | Yes |
| Product Data | |
| Order product name | 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1 |
| Full product name | 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1 |

LED Corn Cobs

| | |
|-------------------------------|--------------|
| Order code | 929003507204 |
| Material Nr. (12NC) | 929003507204 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677579029 |



| | |
|---------------------------------|----------------|
| Numerator - Packs per outer box | 3 |
| EAN/UPC - Case | 50046677579024 |

Dimensional drawing




| Product | D | C |
|--|--------|--------|
| 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1 | 102 mm | 211 mm |

Photometric data



General uniform lighting - 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1



Spectral Power Distribution Colour - 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1



Light Distribution Diagram - 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1

LED Corn Cobs

Lifetime



Life Expectancy Diagram - 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1

Lumen Maintenance Diagram - 150CC/LED/840/LS EX39 G2 BB 277-480V 3/1

